




## AUTOMATIC SLIDE LABELLING



Fast and precise application of plastic film overlays onto microscope slides  
Save time and increase accuracy with Slidebel RVB, for durable and trouble-free operation.

### Why choose Slidebel RVB?

**\*Works on any microscope slide.**

Any kind of slide can be processed.  
No matter color, surface, charge or finish

**\*Fast, precise application**


24 slides per minute.  
High accuracy application

**\*Compact and ergonomic.**

Small footprint of just 34 x 14 cm.  
Easy to use, simple and intuitive

**\* Multi-platform support**

Supports several IHC platforms  
such as Roche Ventana and Dako



Optimal  
for IHC  
platforms



Every slide is perfect with Slidebel RVB!



Durable, chemical and heat resistant overlays are precisely applied onto microscope slides. Any kind of standard slide is supported. No matter color, surface, charge or finish. Automate a large number of manual processes, save time and increase accuracy and productivity.

## Technical specifications

### Specifications

Overlay capacity 2800 slides / label roll  
 Processing speed 24 slides / minute

### Dimensions

Length 34 cm  
 Width 14 cm  
 Height 20 cm  
 Weight 3.5 Kg

### Slide processing

Slide type All standard types  
 ISO 8037  
 Loading mode Cartridge / manual  
 Cartridge capacity 50 slides  
 Slide output delivery Desktop slider /  
 Output tray

### Platform compatibility

Roche Ventana Benchmark  
 Dako Omnis  
 Other IHC platforms